






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		图面升级整理图面	2024.08.31	阿树



SEC:A-A



SEC:B-B



- SPECIFICATIONS
- Voltage rating:125V AC/DC
 - Current rating:1A AC/DC
 - Withstanding Voltage:500V AC/minute
 - Temperature range:−40℃~+125℃
 - Insulation resistance:≥100MΩ
 - Contact resistance:≤20mΩ

PART NO.:

X1002 I-P SN-C
① ② ③ ④ ⑤

- ①Series No
②Category:T-Terminal
③Material:P-Phosphor bronze
④Plating Category:SN-Bright Tin Plating
⑤Type:C

X1002T-PSN-C	Phosphor Bronze	AWG#28-32	X1002T-C
PART NO	Material	Wire Range	Suitable XKB Housing

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	1.0mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X1002T-PSN-C
APPROVED		SIZE:	A4	DWG NO.:	