



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2026.03.03	







Specification

1.VOLTAGE RATING	250V AC/DC.
2.CURRENT RATING	3A AC/DC.
3.WITHSTANDING VOLTAGE	1500V AC/Minute.
4.TEMPERATURE RANGEL	-25 ~+85 .
5. CONTACT RESISTANCE	20 mΩ Max.
6.INSULATION RESISTANCE	1000 MΩ Min.

PART NO.:

X9555 I-P V01-A

Series Number.
Category: T-terminal
Material: P-Phosphorous bronze
Finish:V01-Gold Flash
Other Types A-Tight Type



X9555T-PV01-A	Phosphor Bronze	AWG#22-28	Stamping Before Pating:30u"Ni;70u"Snn	X9555H
PART NO	Material	Wire Range	Finish	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	VIEW:	MODEL TYPE: 2.54mm Pitch Terminal
CHECKED	UNIT: mm/in	PART NO.: X9555T-PV01-A
APPROVED	SIZE: A4	DWG NO.: