






	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.26	阿树



SPECIFICATION
 Contact rating: 50mA,12V DC
 Contact Resistance: 100mΩ max
 Dielectric Strength: 250V AC/1minute
 Travel: 0.25mm
 Operating Temp: -30℃~+85℃
 Storage Temp: -30℃~+80℃

Code-x	H
A	4.30
B	4.50
C	5.00
D	5.50
E	6.00
F	6.50
G	7.00
H	7.50
I	8.00
J	8.50
K	9.00
L	9.50
M	10.00
N	10.50



PAPT NO	TC-1102DE-C-G
Operating Force	A:100gf B:160gf C:260gf
Height	Code-X

⑤	Terminal	3	Brass (0.30t)	Ag Plated
④	Contact	1	F.ag/SUS	
③	Base	1	PPA	
②	Cover	1	Brass	Tin plated
①	Keystake	1	PPA	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW: 	MODEL TYPE: TACT SWITCH		
CHECKED		UNIT: mm/in	PART NO.: TC-1102DE-C-G		
APPROVED		SIZE: A4	DWG NO.: TC-1102DE-C-G		
PRECISION CO., LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A1