






Y型端子



14P-64P 双槽



6P 小鼻/无槽

6P 大鼻/无槽

8P 大鼻/无槽

6P 小鼻/单槽

8P 小鼻/单槽

10P-12P 单槽

TYPE C

TYPE A

TYPE A

TYPE B

TYPE B

Blank

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ MAX

接触电阻: ≤20mΩ MAX

X9555 H1 -2x32- PT V01

① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:H1-two