



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	ECN-P-202410017		注塑模具翻新, 按实物修正产品尺寸, 图框升级	2024.10.28	桑葚
A2	/		修正定位柱开孔尺寸	2025.08.23	阿树





- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:3A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤20mΩ
 - After environmental testing:≤30mΩ

PART NO.:

X9566 W R S-13-9T V01 XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Straight 90°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-02~12Pin
⑥Material:9T-PA9T UL94V-0
⑦Planting: V01:Gold Plated 1u"
⑧Color: Blank-Natural Color



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.54	8.89	5.33	08	17.78	24.13	20.57
03	5.08	11.43	7.87	09	20.32	26.67	23.11
04	7.62	13.97	10.41	10	22.86	29.21	25.65
05	10.16	16.51	12.95	11	25.40	31.75	28.19
06	12.70	19.05	15.49	12	27.94	34.29	30.73
07	15.24	21.59	18.03				

X9556WRS-13-9TV01	PA9T UL 94V-0	Brass	Gold-Flash	X9556H
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	桑 葚	VIEW:	MODEL TYPE: 2.54mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X9556WRS-13-9TV01
APPROVED		SIZE: A4	DWG NO.: