






Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage:1000V AC/minute
耐受电压: 1000V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max

X2511 H - 04 - N0
① ② ③ ④

- 1.Series No
- 2.Category:H-HSG
- 3.Row No.Pin No:XX-02~12P
- 4.Material:N0-Nylon66 94V-0

Poles	Dimensions(mm)		
	A	B	C
02	2.50	5.60	7.30
03	5.00	8.10	9.80
04	7.50	10.60	12.30
05	10.00	13.10	14.80
06	12.50	15.60	17.30
07	15.00	18.10	19.80
08	17.50	20.60	22.30
09	20.00	23.10	24.80
10	22.50	25.60	27.30
11	25.00	28.10	29.80
12	27.50	30.60	32.30

X2511H-04-N0	Nylon66	X2511W	X2511T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



DSND		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector
DWN		VIEW:	PART NO.: X2511H-04-N0
CHKD		UNIT: mm/in	DWG NO.: X-X2511H-04-N0
APPD		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
			SHEET 1/1
			REVISION A0