





#### Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃-+125℃

温度范围: -40℃-+125℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2508 H - 2x04 A - N0

① ② ③ ④ ⑤



1.Series No

2.Category:H-Housing

3.Row No.Pin No:2xXX-2x02~2x20 Pin

4.Special No.

5.Material:N0-Nylon 66 UL94V-0



| Poles | Dimensions(mm) |       | Poles | Dimensions(mm) |       |
|-------|----------------|-------|-------|----------------|-------|
|       | A              | B     |       | A              | B     |
| 2x02  | 2.50           | 9.70  | 2x10  | 22.50          | 30.00 |
| 2x03  | 5.00           | 12.20 | 2x11  | 25.00          | 32.50 |
| 2x04  | 7.50           | 14.70 | 2x12  | 27.50          | 35.00 |
| 2x05  | 10.00          | 17.20 | 2x13  | 30.00          | 37.50 |
| 2x06  | 12.50          | 19.70 | 2x14  | 32.50          | 40.00 |
| 2x07  | 15.00          | 22.20 | 2x15  | 35.00          | 42.20 |
| 2x08  | 17.50          | 24.70 | ...   | ...            | ...   |
| 2x09  | 20.00          | 27.20 | 2x20  | 47.50          | 55.00 |

|                 |          |                    |                       |
|-----------------|----------|--------------------|-----------------------|
| X2508H-2x04A-N0 | Nylon 66 | X2508W-A           | X2508T-A              |
| PART N0         | Material | Suitable XKB Wafer | Suitable XKB Terminal |

|                         |  |                                                                                             |                                            |       |          |
|-------------------------|--|---------------------------------------------------------------------------------------------|--------------------------------------------|-------|----------|
| DSND                    |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.5mm Crimp Style Connector |       |          |
| DWN                     |  | VIEW:  | PART NO.:<br>X2508H-2x04A-N0               |       |          |
| CHKD                    |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X2508H-2x04A-N0              |       |          |
| APPD                    |  | SIZE: A4                                                                                    |                                            |       |          |
| L PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                                     | SHEET | REVISION |
|                         |  |                                                                                             |                                            | 1/1   | A0       |

|                                               |             |      |         |          |                        |      |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                               |             |      |         |          | ANGLAR                 | ±5°  |
| Δx                                            |             |      |         |          | L≤ 4                   | ±0.2 |
| Δx                                            |             |      |         |          | 4<L≤ 16                | ±0.3 |
| Δx                                            |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |      |

**XKB**

XKB INDUSTRIAL PRECISION CO.,LIMITED