







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	① X4	产品尺寸变更, 图面升级整理图面	2024.12.27	阿树



PCB Layout



SECTION A-A



Current rating:5A AC/DC
额定电流: 5A AC/DC
Temperature range:-40℃--+125℃
温度范围: -40℃--+125℃

PART NO.:

- K 137635 W V-2x14-PT SN W
① ② ③ ④ ⑤ ⑥ ⑦ ⑧
- ①K:XKBTEK-Car Connector
②XKB Series No
③Category:W-Wafer
④Welding Board Rangle:V-Stright 180°
⑤Row No.Pin No:2x14 Pin
⑥Material:PT-PBT
⑦Palting:SN-Plated Tin
⑧Color:W-White; B-Black

K137635WV-2x14-PTSNW	PBT	Brass	K137635HM
PART NO	Material	Material(Pin)	Suitable XKB Housing
DESIGN	阿树	VIEW:	MODEL TYPE: 2.2mm Automobile connector
CHECKED		UNIT: mm/in	PART NO.: K137635WV-2x14-PTSNW
APPROVED		SIZE: A4	DWG NO.: X-K137635WV-2x14-PTSNW
SCALE			PAGE
N/A			1/1
REVISION			A1



XKB INDUSTRIAL PRECISION CO.,LIMITED