










由 AUTODESK 学生版生成



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*01	---	5.60	2*07	25.20	30.80
2*02	4.20	9.80	2*08	29.40	35.00
2*03	8.40	14.00	2*09	33.60	39.20
2*04	12.60	18.20	2*10	37.80	43.40
2*05	16.80	22.40	2*11	42.00	47.60
2*06	21.00	26.60	2*12	46.20	51.80



Specifications:

规格: XKB

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:9A AC/DC

额定电流: 9A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ XKB

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X9357 H F -2x04 G-N2

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category:H-HSG
- ③ Welding Board Angle:F-Female
- ④ Row No.-Pin No.:2*XX-2*01P~2*12P
- ⑤ Plug the Pin & special No.:
- I-Without the Wing; G-With the Wing
- ⑥ Material:N0-PA66 94V-0:N2-PA66 94V-2
- ⑦ Color:Blank-Natural Color BK-Black

X9357HF-2x04-N2BK	Nylon 66 94V-2 Black	X9357TM	X9357W Or 9357H	Without Ears
X9357HF-2x04G-N2	Nylon 66 94V-2			With Ears
X9357HF-2x04I-N2	Nylon 66 94V-2			Without Ears
X9357HF-2x04G-N0	Nylon 66 94V-0			With Ears
X9357HF-2x04I-N0	Nylon 66 94V-0			Without Ears
PART NO	Material	Suitable XKB Terminal	Suitable XKB Housing	Note

				XKB	DSND	DATE	SCALE: N/A	MODEL TYPE:
				ANGLAR	DWN	DATE	VIEW:	2.40mm Crimp Style Connectors
				L≤4	CHKD	DATE	UNIT: mm/in	PART NO.:
				4<L≤16	APPD	DATE	SIZE: A4	X9357HF-2x04G-N2
				16<L≤63				DWG NO.:
				L>63				X-X9357HF-2x04G-N2
				UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO.,LIMITED			
				REVISIONS	WEIGHT	SHEET	REVISION	
				www.helloxkb.com	1.0g	1/1	A0	