






接触电阻: $\leq 10\text{m}\Omega$

X1511 H - 03 A - N0
① ② ③ ④ ⑤

- 1.Series No
2.Category:H-HSG
3.Special No:A-There are convex
on both sides
4.Row No.Pin No:XX-02~11P
5.Material:N0-Nylon 66 UL94V-0 ;

Poles	Dimensions(mm)		
	A	B	C
02	1.50	3.55	4.40
03	3.00	5.05	5.90
04	4.50	6.55	7.40
05	6.00	8.05	8.90
06	7.50	9.55	10.40
07	9.00	11.05	11.90
08	10.50	12.55	13.40

X1511H-03A-N0	Nylon 66	X1511W-A	X1511T-A
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

					ANGLAR	$\pm 5^\circ$
ΔX					$L \leq 4$	± 0.2
ΔX					$4 < L \leq 16$	± 0.3
ΔX					$16 < L \leq 63$	± 0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	$L > 63$	± 0.5

UNSPECIFIED TOLERANCES

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X1511H-03A-N0		
CHKD		UNIT: mm/in	DWG NO.: X-X1511H-03A-N0		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0