



PCB LAYOUT

接觸電阻: 20mΩ Max

X8821 W R-03 A -N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
2.Category:W-Wafer
3.Welding Board Angle:R-Straight 90°
4..Row No-Pin No:XX-03P~15P
5.TYPE:A
6.Material:N0-Nylon66 UL94V-0
7.Plating Category:SN-Bright Tin Plating

Poles	Dimensions(mm)	
	A	B
03	5.00	10.00
04	7.50	12.50
05	10.00	15.00
06	12.50	17.50
07	15.00	20.00
08	17.50	22.50
09	20.00	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
15	35.00	40.00

X8821WR-03A-N0SN	Nylon66	Phosphor bronze	X8821H	X8821T
PART NO	Material	Material(PIN)	Suitable XKB Housing	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.5 mm BTB Style Connector		
DWN		VIEW: 	PART NO.: X8821WR-03A-N0SN		
CHKD		UNIT: mm/in	DWG NO.: X-X8821WR-03A-N0SN		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn						

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED