







Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Voltage rating:500V AC/DC

额定电压:500V AC/DC

Current rating:1.0A

额定电流: 1.0A

Insulation resistance:1000MΩ Min

绝缘电阻: 1000MΩ Min

Withstanding voltage:≥500V AC/minute

耐压: ≥500VC/分钟

Temperature range:-40℃~+105℃

使用温度: -40℃~+105℃

X1270 W V S -2x08 A2 - 6T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
② Category:W-wafer
③ Welding Board Angle:V- Straight 180°
④ Welding Way:S-SMT
⑤ Row No.-Pin No.:2xXX-2x03P~2x40P
⑥ A2:1.27x2.54mm
⑦ Material:6T-Nylon PA6T UL94V-0
⑧ Planting Category:V01-All Gold Flash ...
SW-Matte tin

positor	A	B	C
2x03	11.37	9.77	2.54
2x04	12.64	11.04	3.81
2x05	13.91	12.31	5.08
2x06	15.18	13.58	6.35
2x07	16.45	14.85	7.62
2x08	17.72	16.12	8.89
2x09	18.99	17.39	10.16
2x10	20.26	18.66	11.43
2x12	21.53	19.93	12.70
2x13	24.07	22.47	15.24
2x15	26.61	25.01	17.78
2x17	29.15	27.55	20.32
2x20	32.96	31.36	24.13
2x22	35.50	33.90	26.67
2x25	39.31	37.71	30.48
2x30	45.66	44.06	36.83
2x34	50.74	49.14	41.91
2x40	58.36	56.76	49.53

X1270WVS-2x08A2-6TSW	Nylon-6T UL 94V-0	Brass	Matte tin	X1270HA2-08B
X1270WVS-2x08A2-6TV01			Gold Flash	X1270HA2-08A
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Housing

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L≤ 4 ±0.2
ΔX					4<L≤ 16 ±0.3
ΔX					16<L≤ 63 ±0.4
MARK					L> 63 ±0.5
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.27x2.54mmJane cattle简牛		
DWN		VIEW: 	PART NO.: X1270WVS-2x08A2-6TV01		
CHKD		UNIT: mm/in	DWG NO.: X-X1270WVS-2x08A2-6TV01		
APPD		SIZE: A4	WEIGHT	SHEET	REVISION
PRECISION CO.,LIMITED				1/1	A0