



PCB LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压:1500V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -25℃-+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤30mΩ

环境测试后: ≤30兆欧

Max.Processing Temp:240℃ for30-60seconds

(260℃ for10seconds)

X9555 W V S - 2x10 A- 6T V01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:V-Straight 180°

4.Welding Way:S-SMT

5.Row No-Pin No:2xXX-2x05P-2x32P

6.Plug the Pin&Special N0:A-Ejector Header

7.Material:6T-PA6T 94V-0

8.Plating Category:V01-All Gold Flash

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2x05	32.00	10.16	27.94	2x15	57.40	35.56	53.34
2x07	34.54	12.70	33.02	2x17	62.48	40.64	58.42
2x08	39.62	17.78	35.56	2x20	70.10	48.26	66.04
2x10	44.60	22.86	39.70	2x25	82.80	60.96	78.74
2x12	49.78	27.94	45.72	2x30	95.50	73.66	91.44
2x13	52.32	30.48	48.26	2x32	100.58	78.74	96.72

X9555WVS-2x10A-6TV01	PA6T UL 94V-0	Brass	Gold-Flash	X9555H2-2xXXX
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

					DSND		DATE		SCALE: N/A	MODEL TYPE: 2.54mm Horn type connector
ΔX					units: mm	DWN		DATE	VIEW:	PART NO.: X9555WVS-2x10A-6TV01
ΔX					tolerance: X.X ±0.2mm	CHKD		DATE	UNIT: mm/in	DWG NO.: X-X9555WVS-2x10A-6TV01
ΔX					X.XX ±0.1mm	APPD		DATE	SIZE: A4	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm					
REVISIONS					UNSPECIFIED TOLERANCES					
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT 1.0g	SHEET 1/1
										REVISION A0