



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 甚



产品字码标识



规格 Specification:

- 1.额定值 Rating:3A 125/250VAC
- 2.接触电阻 Contact resistance:≤30 mΩ
- 3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
- 4.电气寿命 Electronics life:>10000 cycles
- 5.操作力 Operation force:500±150gf
- 6.所有材料符合Rohs要求 All materials are Rohs compliant


PART NO.:

SS-X 03 12 S G-6 N 2 B B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
- ③ Current Rating: 03-3A;
- ④ Switch Circuit:12-1P2T;
- ⑤ S: Wire bonding;
- ⑥ Handle Shape: G-Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape:N-Square enclosure;
- ⑨ Terminal specs:
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;
4:TYPE-4; 5:TYPE-5;
- ⑩ Handle Colour:
B-Black; W-White; R-Red
- ⑪ Housing Colour:
B-Black; W-White; R-Red



ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 甚	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS-0312SG-6N2BB
APPROVED		SIZE: A4	DWG NO.: X-SS-0312SG-6N2BB
		SCALE	PAGE
		N/A	1/1
		REVISION	A0

XKB INDUSTRIAL PRECISION CO.,LIMITED