



Specifications:
规格:
Voltage rating:150V AC/DC
额定电压: 150V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance: 500MΩ min
绝缘电阻: 500MΩ Min
Contact resistance:30mΩ Max
接触电阻: 30mΩ Max

X9862 H -02 A- N0
 (1) (2) (3) (4) (5)

1.Series No
2.Category:H-HSG
3.Row No.Pin No:XX-02P-30P
4.Special N0:A-With Lock
5.Material:N0-Nylon 66 UL 94V-0



11P~30P



Poles	Dimensions(mm)		
	A	B	C
02	1.25	4.40	2.75
03	2.50	5.65	4.00
04	3.75	6.90	5.25
05	5.00	8.15	6.50
06	6.25	9.40	7.75
07	7.50	10.65	9.00
08	8.75	11.90	10.25
09	10.00	13.15	11.50
10	11.25	14.40	12.75
11	12.50	15.65	14.00
12	13.75	16.90	15.25
13	15.00	18.15	16.50
14	16.25	19.40	17.75
15	17.50	20.65	19.00
20	23.75	26.90	25.25
25	30.00	33.15	31.50
30	36.25	39.40	37.75

X9862H-02A-N0	Nylon 66 UL 94V-0	X9862W-A	X9862T-A
PART N0	Material	Suitable XKB Wafer	Suitable XKB Terminal

XKIE

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X9862H-02A-N0		
CHKD		UNIT: mm/in	DWG NO.: X-X9862H-02A-N0		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISION A0