





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树



Specifications:

规格:

1.Voltage rating:250VAC/DC

额定电压: 250V AC/DC

2.Current rating:3A(T) / 5A(C) AC/DC

额定电流: 3A(T) / 5A(C) AC/DC

3.Withstanding voltage:500V AC/minute

耐受电压: ≥500V AC/分钟

4.Temperature range: -55℃~+105℃

温度范围: -55℃~+105℃

5.Insulation resistance:1000MΩMIN

绝缘电阻: ≥1000MΩ

6.Contact resistance:30mΩMax

接触电阻: ≥30mΩ

Material:

材料:

7.Rubber core:PBT UL94V-0

胶芯: PBT UL94V-0

8.The iron shell:SPCC Nivkel Plating/Tin Plating/Gold Plating

铁壳: SPCC,镀镍/镀锡/镀金

B、成品不能有弯针, R角不一致等不良。

PART NO.:

X02 37 W C 2 W 1

① ② ③ ④ ⑤ ⑥ ⑦

①Series NO.

②Row No.Pin No.XX-09;15;25;37

③Welding Board Angle :W-Male

④T: Tradutional C: Car-pin

⑤Planting Categoty: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U

⑥Color:B-BLACK W-White BL-Blue

⑦1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	30.80	24.99	18.00	19.28
15	39.20	33.32	26.50	27.51
25	53.05	47.04	40.00	41.28
37	69.40	63.50	56.60	57.71

铆合方式	TYPE-1:铆合	TYPE-2:前铆实心螺母	TYPE-7:后铆鱼叉	TYPE-5:铆鱼叉锁螺丝
图示				

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X0237WC2W1
APPROVED		SIZE: A4	DWG NO.: X-X0237WC2W1
		SCALE N/A	PAGE 1/1
			REVISION A1