

1

2

3

4

A

A

B






B

C

C

D

D



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2026.04.10	阿树

PART NO.:

X2026 H-2x04 D-N0 XX
① ② ③ ④ ⑤ ⑥

■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding Voltage:1000V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤30mΩ
- After environmental testing:≤50mΩ

- ①Series No
②Category:H-HSG
③Row No.Pin No:2xXX-2x02~2x22Pin
④Plug the Pin&Special N0:
D-With Lock In the middle
⑤Material:N0-PA66 UL94V-0
⑥Color:Blank-Natural Color;BK-Black

X2026H-2x04D-N0	Nylon 66 UL 94V-0	X2026T-D	X2026H-D
PART NO	Material	Suitable XKB Terminal	Suitable XKB Housing

Poles	Dimensions(mm)					Poles	Dimensions(mm)				
	A	B	C	D	E		A	B	C	D	E
2x02	2.00	6.60	4.60	3.10	3.10	2x10	18.00	22.80	20.60	12.30	9.70
2x03	4.00	8.60	6.60	3.10	3.10	2x11	20.00	24.80	22.60	12.30	9.70
2x04	6.00	10.60	8.60	4.80	2.60	2x12	22.00	26.80	24.60	16.25	13.65
2x05	8.00	12.80	10.60	小扣 4.80	2.30	2x13	24.00	28.80	26.60		
				大扣 7.50	5.00	2x14	26.00	30.80	28.60		
2x06	10.00	14.80	12.60	8.20	5.80	2x15	28.00	32.80	30.60		
2x07	12.00	16.80	14.60	9.70	7.20	2x16	30.00	34.80	32.60		
2x08	14.00	18.80	16.60	小扣 9.70	7.20	2x17	32.00	36.80	34.60		
				大扣 12.30	9.70	2x18	34.00	38.80	36.60		
2x09	16.00	20.80	18.60	小扣 12.30	9.70	2x20	38.00	42.80	40.60		
				大扣 9.70	11.40						

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.00mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X2026H-2x04D-N0
APPROVED		SIZE:	A4	DWG NO.:	

1

2

3

4