






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.12.22	阿树



Specifications:
规格:
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:9A AC/DC
额定电流: 9A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-45℃-+125℃
温度范围: -45℃-+125℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤10mΩ
接触电阻: ≤10mΩ
After environmental testing:≤20mΩ
环境测试后: ≤20mΩ

PART NO.:
X9357 H F-2x03 I-N2 XX
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category:H-HSG
- ③ Welding Board Angle:F-Female
- ④ Row No.-Pin No.:2xXX-2x01P~2x12P
- ⑤ Plug the Pin & special No: I-Without the Wing;
G-With the Wing
- ⑥ Material:N0-PA66 94V-0;N2-PA66 94V-2
- ⑦ Color:Blank-Natural Color BK-Black

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x01	---	5.60	2x07	25.20	30.80
2x02	4.20	9.80	2x08	29.40	35.00
2x03	8.40	14.00	2x09	33.60	39.20
2x04	12.60	18.20	2x10	37.80	43.40
2x05	16.80	22.40	2x11	42.00	47.60
2x06	21.00	26.60	2x12	46.20	51.80

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	4.20mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X9357HF-2x03I-N2
APPROVED		SIZE:	A4	DWG NO.:	