





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.10.13	



Current rating:3A AC/DC
3A AC/DC
Temperature range:-40 -+125
-40 -+125

PART NO.:
K 137635 W R-2x14 B PT SN

K:XKBTEK-Car Connector
XKB Series No
Category:W-Wafer
Welding Board Aagle:R-Straight 90°
Row No.Pin No:2x14 Pin
Special No:B-Misaligned foot
Material:PT-PBT
Palting:SN-Plated Tin



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN		VIEW:	MODEL TYPE: 2.2mm Automobile connector
CHECKED		UNIT: mm/in	PART NO.: K137635WR-2x14B-PTSN
APPROVED		SIZE: A4	DWG NO.: