


3D图示（参考）




■ Specifications.

- Voltage rating: 250V AC/DC
- Current rating: 5A AC/DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25℃ ~ +85℃
- Insulation resistance: 1000mΩ Min
- Contact resistance: 20mΩ Max
- Material: Nylon66 UL94V-0

X5080 H -10- N0

① ② ③ ④

- ① Series No.
- ② Category : H-HSG
- ③ Row No. Pin No. XX-02-12
- ④ Material: N0-Nylon66 94V-0



POLES	A	B
2	5.08	10.16
3	10.16	15.24
4	15.24	20.32
5	20.32	25.40
6	25.40	30.48
7	30.48	35.56
8	35.56	40.64
9	40.64	45.72
10	45.72	50.80
11	50.80	55.88
12	55.88	60.96

X5080H-10-N0	Nylon66 UL 94V-0	X5080T	X5080W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Wafer

					ANGULAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND		SCALE: N/A	MODEL TYPE:		
DWN		VIEW:	5.08mm Crimp Style Connectors		
CHKD		UNIT: mm/in	PART NO.: X5080H-10-N0		
APPD		SIZE: A4	DWG NO.: X-X5080H-10-N0		
			WEIGHT	SHEET	REVISION
				1/1	A0