






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.23	阿树



Circuit diagram






P.C.B LAYOUT




MOUNTING SURFACE


DMX-XXXD-X

1:1A以下
3:3A


1:转换型 SPDT		2:常闭型 SPST-NC		3:常开型 SPST-NO	
					
AuGLAR	±5°				
X.	±0.40				
X.x	±0.30				
X.xx	±0.20				
X.xxx	±0.15				
UNSPECIFIED TOLERANCES					




117




135




150




180




12U




16U




115G



151U



141U



000

DESIGN	阿树	VIEW:		MODEL TYPE:	MICRO SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	DM1-16UD-1
APPROVED		SIZE:	A4	DWG NO.:	X-DM1-16UD-1
				SCALE	PAGE
				N/A	1/1
				REVISION	A1