









	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑葚
A1	N/A		图面升级整理图面	2026.01.05	阿树



PART
NO.: X332A H-28 C-PB XX
(1) (2) (3) (4) (5) (6)

1. Series No: 332A—TYPE A
332B—TYPE B
332C—TYPE C
2. Category: H—Housing
3. Row No. Pin No: XX—See Table A
4. Morphology: Blank—No CPA Feature
C—With CPA Feature
5. Material: PB—PBT
6. Color: Blank—Black; GR—Gray;
BL—Blue

规格Specifications:
 额定电压Voltage rating:60V AC/DC
 额定电流Current rating:3A AC/DC
 耐受电压Withstanding voltage:500V AC/minute
 温度范围Temperature range:-40℃~+125℃
 绝缘电阻Insulation resistance:≥100MΩ
 接触电阻Contact resistance:≤10mΩ (测试后≤30mΩ)



X332CH-XXC-PBXX	X332CWRS-XXC	X332XT-BSN	PBT UL94 V-0
X332BH-XXC-PBXX	X332BWRS-XXC	X332XT-BSN	PBT UL94 V-0
X332AH-XXC-PBXX	X332AWRS-XXC	X332XT-BSN	PBT UL94 V-0
X332CH-XX-PBXX	X332CWRS-XX	X332XT-BSN	PBT UL94 V-0
X332BH-XX-PBXX	X332BWRS-XX	X332XT-BSN	PBT UL94 V-0
X332AH-XX-PBXX	X332AWRS-XX	X332XT-BSN	PBT UL94 V-0
PART NO.	Suitable XKB WAFER	Suitable XKB Terminal	MATERIAL

TABLE A

PIN NO.	A	B	C	D
8	10.00		6.00	15.60
12	14.00	15.90	10.00	19.60
16	18.00	19.90	14.00	23.60
20	22.00	23.90	18.00	27.60
24	26.00	27.90	22.00	31.60
28	30.00	31.90	26.00	35.60
32	34.00	35.90	30.00	39.60
40	42.00	43.90	38.00	47.60


AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	




DESIGN	阿树	VIEW:		MODEL TYPE: 2.0mm Crimp Style Housing						
CHECKED		UNIT:	mm/in	PART NO.: X332AH-28C-PB						
APPROVED		SIZE:	A4	DWG NO.: X-X332AH-28C-PB						
PRECISION CO., LIMITED				<table><tr><td>SCALE</td><td>PAGE</td><td>REVISION</td></tr><tr><td>N/A</td><td>1/3</td><td>A1</td></tr></table>	SCALE	PAGE	REVISION	N/A	1/3	A1
SCALE	PAGE	REVISION								
N/A	1/3	A1								

NO CPA FEATURE

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑葚
A1	N/A		图面升级整理图面	2026.01.05	阿树





8 PIN




12 PIN


MATED DIMENSION




8~12 PIN



16 PIN



20~40 PIN



16~40 PIN

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 2.0mm Crimp Style Housing
CHECKED		UNIT: mm/in	PART NO.: X332AH-28C-PB
APPROVED		SIZE: A4	DWG NO.: X-X332AH-28C-PB

1

2



3

4


WITH CPA FEATURE

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑葚
A1	N/A		图面升级整理图面	2026.01.05	阿树



CPA



16~40 PIN



MATED DIMENSION



16~40 PIN

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.0mm Crimp Style Housing
CHECKED		UNIT:	mm/in	PART NO.:	X332AH-28C-PB
APPROVED		SIZE:	A4	DWG NO.:	X-X332AH-28C-PB

SCALE	PAGE	REVISION
N/A	3/3	A1

1

2

3

4