




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.12	阿树

规格 SPECIFICATIONS:

- 1.电压 / 电流额定值 VOLTAGE/CURRENT RATING: 30V/0.3A AC;
- 2.耐电压 WITHSTANDING VOLTAGE: 100V AC ONE MINUTE;
3. 绝缘电阻 INSULATION RESISTANCE: 50MΩ MIN;
- 4.接触 电阻 CONTACT RESISTANCE: 100mΩ MAX;
- 5.工作 温度范围 OPERATING TEMPERATURE RANGE: -35°C TO 85°C.

材料 MATERIAL:

- 1.绝缘材料 INSULATOR: LCP UL 94V-0 BLACK;
- 2.端子 TERMINAL: COPPER ALLOY;
- 3.金属配件 METAL FITTINGS: COPPER ALLOY.

镀层 PLATING:

- 1.端子 TERMINAL: GOLD PLATING, NICKEL 50u" MIN. OVER ALL;
- 2.金属配件 METAL FITTINGS: TIN 100u" MIN. OVER NICKEL 50u"MIN.

PART NO.:

X0400 W V S-10-LP V01

① ② ③ ④ ⑤ ⑥ ⑦

①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-10~50Pin
⑥PMaterial: LP-LCP 94V-0
⑦Plating Category: V01-Gold Flash

PIN NO.	A	B	C
10	3.80	3.20	1.60
12	4.20	3.60	2.00
16	5.00	4.40	2.80
20	5.80	5.20	3.60
24	6.60	6.00	4.40
30	7.80	7.20	5.60
34	8.60	8.00	5.40
40	9.80	9.20	7.60
50	11.80	11.20	9.60

X0400WVS-10-LPV01	LCP 94V-0	COPPER ALLOY	GOLD PLATING	X0400WVS
PART NO	Material	Material (Terminal)	Finish (Terminal)	Mates With XKB Pin Header
DESIGN	阿树	VIEW:	MODEL TYPE: BTB CONNECTOR	
CHECKED		UNIT: mm/in	PART NO.: X0400WVS-10-LPV01	
APPROVED		SIZE: A4	DWG NO.:	
SCALE			PAGE	REVISION
N/A			1/1	A1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED