




REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A1	N/A		图面升级整理图面	2024.11.30
A2	N/A		图纸更正，产品无变更。	2025.09.15



Specifications(规格):
1.Voltage rating(额定电压): 600V AC/DC
2.Current rating(额定电流):23A AC/DC
3.Withstanding voltage(耐压值):2200V AC/minute
4.Insulation resistance(绝缘电阻):≥100MΩ Min
5.Contact resistance(接触电阻):≤2mΩ Max
6.After environmental testing(测试后接触电阻):≤10mΩ
7.Temperature range(使用温度):−40℃~+125℃

PART NO.:

X5700 W V-2x02-LP SW
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Straight 180°
④Row No.Pin No:2xXX-2x02~2x06Pin
⑤Material:LP-LCP UL94V-0
⑥Planting: SW-Matte tin plating

Poles	Dimensions(mm)		
	A	B	C
2x01	8.35	/	12.34
2x02	12.05	5.70	16.04
2x03	17.75	11.40	21.74
2x04	23.45	17.10	27.44
2x05	29.15	22.80	33.14
2x06	34.85	28.50	38.84

X5700WV-2x02-LPSW	High conductive Brass	X5700H	X5700T
PART NO	Material	Suitable XKB Housing	Suitable XKB Terminal
DESIGN	阿树	VIEW:	MODEL TYPE: Wire to board connector
CHECKED		UNIT: mm/in	PART NO.: X5700WV-2x02-LPSW
APPROVED		SIZE: A4	DWG NO.: X-X5700WV-2x02-LPSW
SCALE		PAGE	REVISION
N/A		1/1	A2

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

