





Poles	Dimensions (mm)	
	A	B
2x01	8.35	
2x02	12.05	5.70
2x03	17.75	11.40
2x04	23.45	17.10
2x05	29.15	22.80
2x06	34.85	28.50

Voltage rating: 600V AC / DC
Current rating: 16A AC / DC
Withstanding voltage: 2200V AC/minute
Temperature range: -40°C~+105°C
Insulation resistance: $\geq 1000M\Omega$
Contact resistance: $\leq 2m\Omega$
After environmental testing : $\leq 10m\Omega$
Special No.: H-High conductive Brass



① ②③ ④ ⑤ ⑥

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : R-Straight 90°
- ④ Row No.-Pin No.: 2xXX-2x02P~2x06P
- ⑤ Material: LP -LCP 94V-0
- ⑥ Plating Category: SW-Matte Tin Plating



Recommended P.C.B Layout
General Tolerance ± 0.05

X5700WR-2x06-LPSW	High conductive Brass	X5700H	X5700T
PART N0	Material	Suitable XKB Housing	Suitable XKB Terminal

General Tolerances:ISO:1101										DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector		
						units:	mm	DWN		DATE		VIEW:		PART NO.: X5700WR-2x06-LPSW			
Δx						tolerance:		CHKD		DATE		UNIT: mm/in		DWG NO.: X-X5700WR-2x06-LPSW			
Δx						X.X	±0.2mm										
Δx						X.XX	±0.1mm										
Δx						X.XXX	±0.05mm										
MARK	DESCRIPTION				DATE	REVISED	APPROVED	X.XXX	±0.05mm	APPD		DATE		SIZE: A4			
REVISIONS								UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	*SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn															1.0g	1/1	A0