



接触电阻: 20mΩ Max

X2001	H3	-2x07	PT	V01
①	②	③	④	⑤

- | Poles | DIM A | DIM B |
|-------|-------|-------|
| 2x03 | 11.20 | 4.00 |
| 2x04 | 13.20 | 6.00 |
| 2x05 | 15.20 | 8.00 |
| 2x06 | 17.20 | 10.00 |
| 2x07 | 19.20 | 12.00 |
| 2x08 | 21.20 | 14.00 |
| 2x09 | 23.20 | 16.00 |
| 2x10 | 25.20 | 18.00 |
| 2x11 | 27.20 | 20.00 |
| 2x12 | 29.20 | 22.00 |
| 2x13 | 31.20 | 24.00 |
| 2x14 | 33.20 | 26.00 |
| 2x15 | 35.20 | 28.00 |
| 2x17 | 39.20 | 32.00 |
| 2x18 | 41.20 | 34.00 |
| 2x20 | 45.20 | 38.00 |
| 2x22 | 49.20 | 42.00 |
| 2x25 | 55.20 | 48.00 |
| 2x30 | 65.20 | 58.00 |

X2001H3-2x07-PTV01	PBT Glass Fiber	Brass	X2001W-B
PART NO	Material	Material(Pin)	Suitable XKB Wafer

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.0mm IDC Connector		
DWN		VIEW: 	PART NO.: X2001H3-2x07-PTV01		
CHKD		UNIT: mm/in	DWG NO.: X-X2001H3-2x07-PTV01		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISION A0