




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		尺寸调整	2024.08.07	阿 树

SPECIFICATION
Contact Rating: 25mA,24V DC
Contact Resistance: 50MΩ max
Insulation Resistance: 100MQ min.500V DC
Dielectric Strength: 500V AC/1minute
Operating Force: 1000gf max
Travel: 0.6mm
Operating Life: 3000cycles
Operating Temp: -20 ~+70
Storage Temp: -30 ~+80

PART NO	NO.OFPOS	DIM.A	Short(S)
DSHP01TS	1	2.87	DSHP01TS-S
DSHP02TS	2	4.14	DSHP02TS-S
DSHP03TS	3	5.41	DSHP03TS-S
DSHP04TS	4	6.68	DSHP04TS-S
DSHP05TS	5	7.95	DSHP05TS-S
DSHP06TS	6	9.22	DSHP06TS-S
DSHP07TS	7	10.49	DSHP07TS-S
DSHP08TS	8	11.76	DSHP08TS-S
DSHP09TS	9	13.03	DSHP09TS-S
DSHP10TS	10	14.30	DSHP10TS-S
DSHP11TS	11	15.57	DSHP11TS-S
DSHP12TS	12	16.84	DSHP12TS-S

4	Terminal		Copper Alloy	T: Tin plated G: Plating Gold
3	Base	1	PPS	Black
2	Keystake	1	PA46	White
1	Cover	1	PPS	Black
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB	DESIGN	阿 树	VIEW:	MODEL TYPE: DIP SWITCH	
	CHECKED		UNIT: mm/in	PART NO.: DSHP04TS-S	
	APPROVED		SIZE: A4	DWG NO.: X-DSHP04TS-S	
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE N/A	PAGE 1/1
				REVISION A1	