










	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2024.12.16	

Specifications:
Voltage rating:50V AC/DC
Current rating:2A AC/DC
Withstanding voltage:500V AC/minute
Temperature range:-40 +125
Insulation resistance: $\geq 100\text{M}\Omega$ MIN
Contact resistance:20m Ω MAX
After environmental testing 20m Ω Max

PART NO.:

X1203 W R S-02-6T V01

Series No
Category:W-Wafer
Welding Board Angle:R-Sright 90°
Welding Way: S-SMT
Row No.Pin No:XX-02~03Pin
Material:NO-PA6T UL94V-0;
LP-LCP UL94V-0;
Plating Category: V01-All Gold Flash

Poles	Dimensions(mm)			
	A	B	C	D
02	1.20	2.70	4.20	3.20
03	2.40	3.90	5.40	4.40

X1203WRS-XX-6TV01	N0-PA6T 94V-0	Phosphor Bronze	Gold Flash	X1203H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKIB 星城 Connection

DESIGN		VIEW: 	MODEL TYPE: 1.20mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X1203WRS-02-6TV01
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1