





接触电阻: 20mΩ Max



PCB Layout



3~16 Pin样式

X8821	W	V	S - 07 - 9T	SN
(1)	(2)	(3)	(4) (5) (6)	(7)

1.Series No
2.Category:W-Wafer
3.Welding Board Angle:V-Stright 180°
4.Welding Way:S-SMT
5.Row No.Pin No:XX-02~10P
6.Material:9T-PA9T UL94V-0
7.Plating:SN-TiN Plated

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.50	7.45	10.00	10	22.50	27.45	30.00
03	5.00	9.95	12.50	11	25.00	29.95	32.50
04	7.50	12.45	15.00	12	27.50	32.45	35.00
05	10.00	14.95	17.50	13	30.00	34.95	37.50
06	12.50	17.45	20.00	14	32.50	37.45	40.00
07	15.00	19.95	22.50	15	35.00	39.95	42.50
08	17.50	22.45	25.00	16	37.50	42.45	45.00
09	20.00	24.95	27.50				

X8821WVS-07-9TSN	PA9T	Brass	X8821H
PART N0	Material	Material(Brass)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X8821WVS-07-9TSN
CHKD		UNIT: mm/in	DWG NO.: X-X8821WVS-07-9TSN
APPD		SIZE: A4	

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn						

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0