



| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /          | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2025.05.22 | 阿树     |



PART NO.:

X02 37 F I 7 BL 5  
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.  
②Row No.Pin No.XX-09;15;25;37  
③Welding Board Angle :F-Female  
④T: Tradutonal C: Car-pin  
⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U'  
5:15U' 6:30U' 7:AU Sn  
⑥Color:B-BLACK W-White BL-Blue  
⑦1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7

#### Specifications:

规格:

1.Voltage rating:250VAC/DC

额定电压: 250V AC/DC

2.Current rating:1A AC/DC

额定电流: 1A AC/DC

3.Withstanding voltage:500V AC/minute

耐受电压: ≥500V AC/分钟

4.Temperature range: -55℃--+105℃

温度范围: -55℃--+105℃

5.Insulation resistance:1000MΩMIN

绝缘电阻: ≥1000MΩ

6.Contact resistance:30mΩMax

接触电阻: ≥30mΩ

Material:

材料:

7.Rubber core:PBT UL94V-0



胶芯: PBT UL94V-0

8.The iron shell:SPCC Nivkel Plating/Tin Plating/Gold Plating

铁壳: SPCC,镀镍/镀锡/镀金

B、成品不能有弯针，R角不一致等不良。

| NUMBER OF POSITIONS | DIMENSION |        |        |        |
|---------------------|-----------|--------|--------|--------|
|                     | A±0.25    | B±0.13 | C±0.38 | D±0.25 |
| 9                   | 30.80     | 24.99  | 16.35  | 19.28  |
| 15                  | 39.20     | 33.32  | 24.75  | 27.51  |
| 25                  | 53.05     | 47.04  | 38.35  | 41.28  |
| 37                  | 69.40     | 63.50  | 54.75  | 57.71  |



| 铆合方式 | TYPE-1:铆合 | TYPE-2:前铆实心螺母 | TYPE-7:后铆鱼叉 | TYPE-5:铆鱼叉锁螺丝 |
|------|-----------|---------------|-------------|---------------|
| 图示   |           |               |             |               |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |

**XKB** 星树  
Connection

|          |    |             |                        |
|----------|----|-------------|------------------------|
| DESIGN   | 阿树 | VIEW:       | MODEL TYPE: D-SUB      |
| CHECKED  |    | UNIT: mm/in | PART NO.: X0237FT7BL5  |
| APPROVED |    | SIZE: A4    | DWG NO.: X-X0237FT7BL5 |
|          |    | SCALE N/A   | PAGE 1/1               |
|          |    |             | REVISION A1            |