



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.11.26	阿树



Specifications:
规格:
Voltage rating:100V AC/DC
额定电压: 100V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃
Insulation resistance: $\geq 500M\Omega$
绝缘电阻: $\geq 500M\Omega$
Contact resistance: $\leq 30m\Omega$
接触电阻: $\leq 30m\Omega$
After environmental testing: $\leq 40m\Omega$
环境测试后: ≤ 40 兆欧

PART NO.:
X1008 H-30-46 XX
① ② ③ ④ ⑤

- ①Series No
②Category:H-HSG
③Row No.Pin No:XX-08~30Pin
④Material:46-PA46 UL94V-0;
LP-LCP 94V-0
⑤Color:Blank-natural color

Circuit 1

Poles	Dimensions(mm)				PART NO	Material	Material(Shell)	Suitable XKBTerminal	Suitable XKBTerminal
	A	B	C	D					
8	7.00	11.50	9.85	8.50	X1008H-XX-LP	LCP UL 94V-0	Stainless Steel	X1008T	X1008W
20	19.00	23.50	21.85	20.50	X1008H-30-46	Nylon 46 UL 94V-0			
30	29.00	33.50	31.85	30.50					

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	1.00mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X1008H-30-46
APPROVED		SIZE:	A4	DWG NO.:	