


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.12.22	阿树



- Specifications
- Voltage rating:600V AC/DC
 - Current rating:9A AC/DC
 - Withstanding voltage:1500V AC/minute
 - Temperature range:-45° to+125°
 - Insulation resistance:≥1000MΩ Min
 - Contact resistance:≤10mΩ Max
 - After environmental testing:≤20mΩ

PART NO.:
X9357 T F-P SN-H
① ② ③ ④ ⑤ ⑥

① Series No
② Category:T-terminal
③ Shape:F-Female
④ Material:P-Phosphor bronze;B-Brass
⑤ Plating style: SN-Bright tin plating
⑥ Special No: H-High Leads

X9357TF-BSN-H	Brass	AWG#16-24	3.10mm(Max)	Stamping Before Plating :30u" MIN. Ni70u"Sn MIN.	X9357HM
X9357TF-PSN-H	Phosphor Bronze				
PART NO	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN 阿树

CHECKED

APPROVED

VIEW: 

UNIT: mm/in

SIZE: A4

MODEL TYPE:
4.20 mm Crimp Style Connector

PART NO.:
X9357TF-PSN-H

DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1