



- Voltage rating: 250V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000\text{M}\Omega$
- Contact resistance: $\leq 20\text{m}\Omega$
- After environmental testing: $\leq 30\text{m}\Omega$

① ② ③ ④

- ① SeriesNumber
② Category : H-HSG
③ Row No.Pin No:xx-02-15P
④ Material:N0-PA66 UL 94V-0



X2012H-06-N0	PA66 UL 94V-0	X2012T	X2012W
PARY N0	Matrial	Suitable XKB Terminal	Suitable XKB Wafer

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors			
ΔX						ANGULAR $L \leq 4$	$\pm 5^\circ$ ± 0.2	DWN		DATE		VIEW: 	PART NO.: X2012H-06-N0		
ΔX						$4 < L \leq 16$	± 0.3	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2012H-06-N0		
ΔX						$16 < L \leq 63$	± 0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION				DATE	REVISED	APPROVED				X-X2012H-06-N0				
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED			
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												WEIGHT 1.0g	SHEET 1/1	REVISION A0	