





XKB

由 AUTODESK 学生版生成



P.C.B LAYOUT

Specifications:

规格: XKB  
Voltage rating:600V AC/DC  
额定电压: 600V AC/DC  
Current rating:9A AC/DC  
额定电流: 9A AC/DC  
Withstanding voltage:1500V AC/minute  
耐受电压: 1500V AC/分钟  
Temperature range:-25℃-+85℃  
温度范围: -25℃-+85℃  
Insulation resistance:≥1000MΩ  
绝缘电阻: ≥1000MΩ  
Contact resistance:≤10mΩ  
接触电阻: ≤10mΩ  
After environmental test:≤20mΩ  
环境测试后: ≤20兆欧

X9357 WV X-2x12 HB-N0 SN

- 01 Series No  
02 Category:W-wafer  
03 Welding Board Angle:V-Straight 180°  
04 Welding Way: Blank-DIP  
05 Row No.-Pin No: 2\*XX-2\*02P-2\*12P  
06 Plug the Pin&Specal NO.:  
HB-The hollow needle with positioning column  
arrange ushering  
07 Material:NO-PA66 94V-0:N2-PA66 94V-7  
08 Planting Category:SN-Bright tin plating  
09 Color:Blank-Natural Color

| Poles | Dimensions(mm) |       | Poles | Dimensions(mm) |       |
|-------|----------------|-------|-------|----------------|-------|
|       | A              | B     |       | A              | B     |
| 2*02  | 4.20           | 15.10 | 2*08  | 29.40          | 40.30 |
| 2*03  | 8.40           | 19.30 | 2*09  | 33.60          | 44.50 |
| 2*04  | 12.60          | 23.50 | 2*10  | 37.80          | 48.70 |
| 2*05  | 16.80          | 27.70 | 2*11  | 42.00          | 52.90 |
| 2*06  | 21.00          | 31.90 | 2*12  | 46.20          | 57.10 |
| 2*07  | 25.20          | 36.10 |       |                |       |

|                     |                   |               |             |                      |
|---------------------|-------------------|---------------|-------------|----------------------|
| X9357WV-2x12HB-N0SN | Nylon 66 UL 94V-0 | Brass         | Tin-Plated  | X9357HM-B            |
| X9357WV-2x12HB-N2SN | Nylon 66 UL 94V-2 | Brass         | Tin-Plated  | X9357HM-B            |
| PART N0             | Material          | Material(Pin) | Finish(Pin) | Suitable XKB Housing |

|                  |             |  |  |      |           |          |                        |  |      |  |                                                                                             |                                              |       |          |
|------------------|-------------|--|--|------|-----------|----------|------------------------|--|------|--|---------------------------------------------------------------------------------------------|----------------------------------------------|-------|----------|
| XKB              |             |  |  |      |           |          | DSND                   |  | DATE |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.40mm Crimp Style Connectors |       |          |
|                  |             |  |  | XKB  | ANGLAR    | ±5°      | DWN                    |  | DATE |  | VIEW:  | PART NO.:<br>X9357WV-2x12HB-N0SN             |       |          |
| Δx               |             |  |  |      | L ≤ 4     | ±0.2     | CHKD                   |  | DATE |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X9357WV-2x12HB-N0SN            |       |          |
| Δx               |             |  |  |      | 4<L ≤ 16  | ±0.3     |                        |  |      |  |                                                                                             |                                              |       |          |
| Δx               |             |  |  |      | 16<L ≤ 63 | ±0.4     |                        |  |      |  |                                                                                             |                                              |       |          |
| MARK             | DESCRIPTION |  |  | DATE | REVISED   | APPROVED | APPD                   |  | DATE |  | SIZE: A4                                                                                    |                                              |       |          |
| REVISIONS        |             |  |  |      |           |          | UNSPECIFIED TOLERANCES |  |      |  |                                                                                             | XKB INDUSTRIAL PRECISION CO.,LIMITED         |       |          |
| www.helloxkb.com |             |  |  |      |           |          |                        |  |      |  |                                                                                             |                                              |       |          |
|                  |             |  |  |      |           |          |                        |  |      |  |                                                                                             | WEIGHT                                       | SHEET | REVISION |
|                  |             |  |  |      |           |          |                        |  |      |  |                                                                                             | 1.0g                                         | 1/1   | A0       |