




Poles	Dimensions (mm)	
	A	B
2x01	8.35	
2x02	12.05	5.70
2x03	17.75	11.40
2x04	23.45	17.10
2x05	29.15	22.80
2x06	34.85	28.50




Specifications:

Voltage rating: 600V AC / DC
Current rating: 16A AC / DC
Withstanding voltage: 2200V AC/minute
Temperature range: -40°C~+105°C
Insulation resistance: $\geq 1000\text{M}\Omega$
Contact resistance: $\leq 2\text{m}\Omega$
After environmental testing : $\leq 10\text{m}\Omega$
Special No.: H-High conductive Brass



X5700 W R -2x05 -LP SW

- ① Series No.
② Category : W-WAFER
③ Welding Board Angle : R-Straight 90°
④ Row No.-Pin No.: 2xXX-2x02P~2x06P
⑤ Material: LP -LCP 94V-0
⑥ Plating Category: SW-Matte Tin Plating



Recommended P.C.B Layout
General Tolerance±0.05

X5700WR-2x05-LPSW	High conductive Brass	X5700H	X5700T
PART NO	Material	Suitable XKB Housing	Suitable XKB Terminal

										DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector			
						units:	mm			DWN		DATE		VIEW: 	PART NO.: X5700WR-2x05-LPSW			
Δx						tolerance:				CHKD		DATE		UNIT: mm/in	DWG NO.: X-X5700WR-2x05-LPSW			
Δx							X.X ±0.2mm					DATE						
Δx							X.XX ±0.1mm					DATE						
Δx							X.XXX ±0.05mm			APPD		DATE		SIZE: A4				
MARK	DESCRIPTION				DATE	REVISED	APPROVED											
REVISIONS								UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g	•SHEET 1/1	REVISION A0
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																		