




P.C.B LAYOUT



剖面



#### Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃--+105℃

温度范围: -40℃--+105℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2001 W V S - 2x17 B - 6T V01  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Stright 180°

4.Welding Way: S-SMT

5.Row No.Pin No: 2xXX-2x03-2x32P

6.Category:B-Have gaps

7.Material:6T-Nylon 6T UL 94V-0

8.Plating:V01-Gold Flash

| Poles | Dimensions |       | Poles | Dimensions |       |
|-------|------------|-------|-------|------------|-------|
|       | A          | B     |       | A          | B     |
| 2x03  | 4.00       | 13.30 | 2x13  | 24.00      | 33.30 |
| 2x04  | 6.00       | 15.30 | 2x15  | 28.00      | 37.30 |
| 2x05  | 8.00       | 17.30 | 2x17  | 32.00      | 41.30 |
| 2x06  | 10.00      | 19.30 | 2x18  | 34.00      | 43.30 |
| 2x07  | 12.00      | 21.30 | 2x20  | 38.00      | 47.30 |
| 2x08  | 14.00      | 23.30 | 2x22  | 42.00      | 51.30 |
| 2x09  | 16.00      | 25.30 | 2x25  | 48.00      | 57.30 |
| 2x10  | 18.00      | 27.30 | 2x30  | 58.00      | 67.30 |
| 2x12  | 20.00      | 31.30 | /     |            |       |

|                      |          |               |                  |
|----------------------|----------|---------------|------------------|
| X2001WVS-2x17B-6TV01 | Nylon 6T | Brass         | X2001HA3-2x17    |
| PART NO              | Material | Material(Pin) | Suitable XKB IDC |

| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|
| ΔX                                            |             |      |         |          | ANGLAR ±5°             |
| ΔX                                            |             |      |         |          | L≤ 4 ±0.2              |
| ΔX                                            |             |      |         |          | 4<L≤ 16 ±0.3           |
| ΔX                                            |             |      |         |          | 16<L≤ 63 ±0.4          |
| MARK                                          |             |      |         |          | L> 63 ±0.5             |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |

|                                      |             |                                 |
|--------------------------------------|-------------|---------------------------------|
| DSND                                 | SCALE: N/A  | MODEL TYPE:                     |
| DWN                                  | VIEW:       | 2.0mm Jane cattle 简牛            |
| CHKD                                 | UNIT: mm/in | PART NO.: X2001WVS-2x17B-6TV01  |
| APPD                                 | SIZE: A4    | DWG NO.: X-X2001WVS-2x17B-6TV01 |
| XKB INDUSTRIAL PRECISION CO.,LIMITED |             | WEIGHT                          |
|                                      |             | SHEET 1/1                       |
|                                      |             | REVISION A0                     |