



Voltage rating:500V AC/DC

额定电压:500V AC/DC

Current rating:1.0A

额定电流: 1.0A

Insulation resistance:1000MΩ Min

绝缘电阻: 1000MΩ Min

Withstanding voltage:≥500V AC/minute

耐压: ≥500VC/分钟

Temperature range:-40℃-+105℃

使用温度: -40℃-+105℃

X1270 W V -2x12 C - 6T V01  
① ② ③ ④ ⑤ ⑥ ⑦

① Series No.

② Category:W-wafer

③ Welding Board Angle:V- Straight 180°

④ Row No.-Pin No.:2xXX-2x03P~2x32P

⑤ C:With Horns

⑥ Material:6T-Nylon PA6T UL94V-0

⑦ Planting Category:V01-All Gold Flash

| NUMBER<br>OF POSITIONS | DIMENSIONS |       |
|------------------------|------------|-------|
|                        | A          | B     |
| 2x03                   | 2.54       | 18.31 |
| 2x04                   | 3.81       | 19.58 |
| 2x05                   | 5.08       | 20.85 |
| 2x06                   | 6.35       | 22.12 |
| 2x07                   | 7.62       | 23.39 |
| 2x08                   | 8.89       | 24.66 |
| 2x09                   | 10.16      | 25.93 |
| 2x10                   | 11.42      | 27.20 |
| 2x12                   | 13.97      | 29.74 |
| 2x13                   | 15.24      | 31.01 |
| 2x15                   | 17.78      | 33.55 |
| 2x17                   | 20.32      | 36.09 |
| 2x20                   | 24.13      | 39.90 |
| 2x25                   | 30.48      | 46.25 |
| 2x30                   | 36.83      | 52.60 |
| 2x32                   | 39.37      | 55.14 |

|                     |               |                               |                             |                      |
|---------------------|---------------|-------------------------------|-----------------------------|----------------------|
| X1270WV-2x12C-6TV01 | PA6T UL 94V-0 | Brass                         | Gold Flash                  | X1270H-2x12          |
|                     |               |                               |                             | X1270H1-2x12         |
| PART NO             | Material      | Material(Pin And Solder Tabs) | Finish(Pin And Solder Tabs) | Suitable XKB Housing |

|      |  |             |                                    |       |
|------|--|-------------|------------------------------------|-------|
| DSND |  | SCALE: N/A  | MODEL TYPE:<br>Horn type connector |       |
| DWN  |  | VIEW:       | PART NO.:<br>X1270WV-2x12C-6TV01   |       |
| CHKD |  | UNIT: mm/in | DWG NO.:<br>X-X1270WV-2x12C-6TV01  |       |
| APPD |  | SIZE: A4    |                                    |       |
|      |  |             | WEIGHT                             | SHEET |
|      |  |             | 1/1                                | A0    |

|                                               |             |      |         |          |                        |      |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                               |             |      |         |          | ANGLAR                 | ±5°  |
| Δx                                            |             |      |         |          | L≤ 4                   | ±0.2 |
| Δx                                            |             |      |         |          | 4<L≤ 16                | ±0.3 |
| Δx                                            |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |      |

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED