






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	
A1	N/A			2026.01.05	



3D VIEW




WINDING DIRECTION AFTER STAMPING


PART NO.:
X332B I-B SN

- 1.Series No:332A-TYPE A
332B-TYPE B
- 2.Category:T-Terminal
- 3.Material:B-Copper Alloy
- 4.Finish:SN-Tin-plated

Specifications:
Voltage rating:60V AC/DC
Current rating:3A AC/DC
Withstanding voltage:500V AC/minute
Temperature range:-40 ~+125
Insulation resistance:≥ 100MΩ
Contact resistance:≤ 10mΩ ≤ 30mΩ
Material:Copper Alloy,T=0.15mm
Finish:Tin 40~120u" Overall



SECTION A-A



SECTION B-B

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

X332BT-BSN	X332XH-XXX-PB	0.50mm ² (20AWG) OD=1.60 Max	1.80	1.92
X332AT-BSN	X332XH-XXX-PB	0.22~0.35mm ² (22~24AWG) OD=1.50 Max	1.46	1.74
PART NO.	SUITABLE XKB HOUSING	WIRE SIZE	DIM A	DIM A



DESIGN	VIEW:	MODEL TYPE: 2.0mm Crimp Style Housing
CHECKED	UNIT: mm/in	PART NO.: X332BT-BSN
APPROVED	SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1