



1

2


3

4




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.08.06	阿 树
A2	N/A		产品图纸变更	2024.08.22	阿 树



WITHOUT DRAIN HOLES



P.C.B LAYOUT



Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:7A AC/DC

额定电流: 7A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-45℃~+125℃

温度范围: -45℃~+125℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

PART NO.:

X9357 W V-2x03 HS-N2 SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

① Series No

② Category:W-Wafer

③ Welding Board Angle:V-Straight 180°

④ Row No-Pin No: 2xXX-2x01~2x02pin

⑤ Plug the Pln&Specal NO.:HS-Hollow needle seal

⑥ Material:N2-PA66 94V-2

⑦ Planting Category:SN-Bright Tin plating

⑧ Color:Blank-Natural Color

Poles	Dimensions (mm)	
	A	B
2x01	--	5.60
2x02	4.20	9.80
2x03	8.40	14.00
2x04	12.60	18.20
2x05	16.80	22.40
2x06	21.00	26.60
2x07	25.20	30.80
2x08	29.40	35.00
2x09	33.60	39.20
2x10	37.80	43.40
2x11	42.00	47.60
2x12	46.20	51.80

X9357WV-2x03HS-N2SN	Nylon 66 UL 94V-2	Brass	Tin-Plated	X9357H
PARE NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿 树	VIEW:	MODEL TYPE: 4.20 mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9357WV-2x03HS-N2SN
APPROVED		SIZE: A4	DWG NO.: X-X9357WV-2x03HS-N2SN
		SCALE	PAGE
		N/A	1/1
		REVISION	A2

1

2

3

4