








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.13	阿树




A




B




C




2x06PIN




2x07PIN




2x02PIN



2x03PIN



2x04PIN



2x05PIN

Specifications:
规格:
Voltage rating:400V AC/DC
额定电压: 400V AC/DC
Current rating:14A AC/DC
额定电流: 14A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-40℃+125℃
温度范围: -40℃+125℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:15mΩ Max
接触电阻: 15mΩ Max

PART NO.:

X3501 W V-2x06 B S-LP SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:V-Stright 180°
- ④Row No.Pin No:2xXX-2x02~2x12P
- ⑤Category:A Key Black ; B Key Nature
- ⑥TYPE:S-With positioning column
- ⑦Material:LP-LCP UL94V-0
- ⑧Plating:SN-Tin Plated;V01-Gold Flash

Poles	Dimensions	
	A	B
2x02	3.50	8.00
2x03	7.00	11.50
2x04	10.50	15.00
2x05	14.00	18.50
2x06	17.50	22.00
2x07	21.00	25.50
2x08	24.50	29.00
2x12	38.50	43.00

D

X3501WV-2x06BS-LPSN	LCP	Copper Alloy	WV-2x06AS	X3501H-2x06A / X3501H-2x06A0
			WV-2x06BS	X3501H-2x06B / X3501H-2x06B0
PART NO	Material	Material(Pin)	Category	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE:	3.5mm Crimp Style Connector
PART NO.:	X3501WV-2x06BS-LPSN
DWG NO.:	