




PCB LAYOUT



Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage: 300V AC/minute

耐受电压: 300V AC/分钟

Temperature range: -40°C~+105°C

温度范围: -40°C~+105°C

Insulation resistance: ≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Wave soldering temperature: 255±5°C, 10S

波峰焊温度: 255±5°C, 10S

| X1322 | W | V | - 2x04 | H | - C40 | D30 | - E80 |
|-------|---|---|--------|---|-------|-----|-------|
| ①     | ② | ③ | ④      | ⑤ | ⑥     | ⑦   | ⑧     |

1. Series No.

2. Category: W-Water

3. Welding Board Angle: V-Straight 180°

4. Row No -Pin No: 2xXX-2x01P-2x40P

5. Plastic height: J=1.0 mm K=1.5mm I=2.0mm

H=2.5mm D=3.0mm E=3.5mm

F=4.0mm W=5.0mm .....

6. Pin length: C=4.0mm .....

7. Pin length: D=3.0mm .....

8. Pin length: E=(Plastic height + Plastic height+A)

9. Planting Category: Blank=gold plating 1U"

SN=Plating Tin

AuSn=Terminal half-AuSn

V03=Plating 3U"

V15=Plating 15U"

V30=Plating 30U" .....

|                          |          |               |                        |
|--------------------------|----------|---------------|------------------------|
| X1322WV-2x04H-C40D30-E80 | PA6T     | Brass         | X1321F                 |
| PART NO                  | Material | Material(Pin) | Suitable XKB<br>Female |

|                       |  |                                                                                             |                                        |       |          |
|-----------------------|--|---------------------------------------------------------------------------------------------|----------------------------------------|-------|----------|
| DSND                  |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>1.27mm BTB Connector    |       |          |
| DWN                   |  | VIEW:  | PART NO.:<br>X1322WV-2x04H-C40D30-E80  |       |          |
| CHKD                  |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X1322WV-2x04H-C40D30-E80 |       |          |
| APPD                  |  | SIZE: A4                                                                                    |                                        |       |          |
| PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                                 | SHEET | REVISION |
|                       |  |                                                                                             |                                        | 1/1   | A0       |

|                                               |  |  |  |  |                        |      |
|-----------------------------------------------|--|--|--|--|------------------------|------|
|                                               |  |  |  |  | ANGULAR                | ±5°  |
| ΔX                                            |  |  |  |  | L ≤ 4                  | ±0.2 |
| ΔX                                            |  |  |  |  | 4 < L ≤ 16             | ±0.3 |
| ΔX                                            |  |  |  |  | 16 < L ≤ 63            | ±0.4 |
| MARK                                          |  |  |  |  | L > 63                 | ±0.5 |
| REVISIONS                                     |  |  |  |  | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |  |  |  |  |                        |      |

XKB

XKB INDUSTRIAL PRECISION CO., LIMITED