





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.2	阿树



SECTION: A-A
SCALE: 1:1



SECTION: B-B
SCALE: 1:1

Temperature range: -40°C ~ +125°C
温度范围: -40°C ~ +125°C

PART NO.:

K 284162 I M-P SN-H
① ② ③ ④ ⑤ ⑥ ⑦

- ①K:XKBTEK-Car Connector
②XKB Series No
③Category:T-Terminal
④Category:M-Male Terminal
⑤Material:P-Phosphor Bronze
⑥Plating:SN-Plated Tin
⑦Special No:H-High foot

K284162TM-PSN-H	Phosphor Bronze	AWG#18~14	K284162HF
PART NO	Material	Wire Range	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	5.0mm Automobile connector
CHECKED		UNIT:	mm/in	PART NO.:	K284162TM-PSN-H
APPROVED		SIZE:	A4	DWG NO.:	X-K284162TM-PSN-H

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1