




LEFT SIDE VIEW




FRONT VIEW




BOTTOM VIEW




RIGHT SIDE VIEW




RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE



TOP VIEW



BACK VIEW



LED Specification

XKB Connectivity

MATERIAL 材料:

HOUSING 外壳: PBT,UL94V-0,BLACK. HF

TERMINALS BRACKET 端子支架: PBT,UL94V-0,BLACK. HF

SHIELD 保护物: C2680,T=0.20MM,NICKEL PLATING ON ALL AREA.

TERMINAL 端子: PHOSPHOR BRONZE C5210, T=0.35MM,
GOLD PLATING ON CONTACT AREA.

MECHANICAL 机械:

DURABILITY 耐用性: 750 CYCLES MIN.

MATING FORCE 配合力: 23N MAX.

OPERATING TEMPERATURE 工作温度: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.

STORAGE TEMPERATURE 儲存溫度: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.

ALL CRITICAL DIMENSIONS WITH ".001"

DSND		SCALE: N/A	MODEL TYPE: RJ JACK		
DWN		VIEW: 	PART NO.:		
CHKD		UNIT: mm/in	DWG NO.:		
APPD		SIZE: A4	X01AQ070CA2AD		
PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED