





由 AUTODESK 学生版生成



■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ
- Mark "*"Indicate Dimensions Need To Controlled In Emphasis

P.C.B. LAYOUT



X3025 W V S- 10 C-LPSW

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

⑪ Series No.

⑫ Category :

W-wa fer

⑬ Welding Board Angle:

V-180°

⑭ Welding Way:

S-SMT

⑮ Row No.-Pin No.

XX-Single row

⑯ Special NO.

C-The ha fPoon

⑰ Material:

LP-LCP 94V-0 66-PA66 94V-0

⑱ Planting Category:

V**All Gold-Plated

G**Gold-Plated Contact

*01-Gold Flash ; *02-2U" ; *03-3U" ; *05-5U"

*10-10U" ; *15-15U" ; *30-30U" ; *50-50U"

SN-Bright tin plating 70U"

SN1-Bright tin plating 120U"Min. ;

SW-Fog Tin plating

⑲ Color:

Blank-natural color

Poles	Dimensions (mm)		
	A	B	C
02	6.85	3.00	7.30
03	9.85	6.00	10.30
04	12.85	9.00	13.30
05	15.85	12.00	16.30
06	18.85	15.00	19.30
07	21.85	18.00	22.30
08	24.85	21.00	25.30
09	27.85	24.00	28.30
10	30.85	27.00	31.30
11	33.85	30.00	34.30
12	36.85	33.00	37.30

X3025 WVS-10C-LPSW	LCP UL 94V-0	Brass	Tin Plating Fog	Brass	Tin-Plated	X3025H
X3025 WVS-10C-66SN	PA66 UL 94V-0	Brass	Tin-Plated	Brass	Tin-Plated	X3025H
PART NO	Material	Material(pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	Mates With XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors		
Δx				XKB	ANGLAR	±5°	DWN		DATE		VIEW:	PART NO.: X3025WVS-10C-LPSW		
Δx					4<L≤16	±0.3	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X3025WVS-10C-LPSW		
Δx					16<L≤63	±0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED						L>63	±0.5	
REVISIONS							UNSPECIFIED TOLERANCES							
www.helloxkb.com							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g	SHEET 1/1	REVISION A0