



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		料号说明pin数修改	2024.07.27	阿树
A2	N/A		独立各PIN数图纸, 增加开孔定位尺寸	2024.12.10	阿树

Specifications:

- Voltage rating:250V AC/DC
额定电压: 250V AC/DC
- Current rating:3A AC/DC
额定电流:3A AC/DC
- Withstanding voltage:500V AC/minute
耐受电压:500V AC/分钟
- Temperature range:-55℃~+105 ℃
温度范围:-55℃~+105 ℃
- Insulation resistance:≥1000MΩ
绝缘电阻:≥1000MΩ
- Contact resistance:≤30mΩ
接触电阻:≤30mΩ
- Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
- The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC-SD, 镀镍/镀锡/镀金
- Terminal:Copper alloy
端子: 铜合金



PART NO.:

X04 62 W C 2 W 1
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Row No-Pin No: 62Pin
- ③Welding Board Angle:W-Male
- ④T:Tradutional C:Car-pin
- ⑤Planting Catogtry:
1:1u 2:2u 3:3u 4:5u 5:15u 6:30u 7:AuSn
- ⑥Color:B-Black W-White BL-Blue
- ⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树	VIEW: 	MODEL TYPE: D-SUB		
CHECKED		UNIT: mm/in	PART NO.: X0462WC2W1		
APPROVED		SIZE: A4	DWG NO.: X-X0462WC2W1		
PRECISION CO.,LIMITED			SCALE N/A	PAGE 1/1	REVISION A2