





REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	30.80	24.99	18.00	19.28
15	39.20	33.32	26.50	27.51
25	53.05	47.04	40.00	41.28
37	69.40	63.50	56.60	57.71

铆合方式		TYPE-1: 铆合	TYPE-2: 前铆实心螺母	TYPE-7: 后铆鱼叉	TYPE-5: 铆鱼叉锁螺丝	
图示						
DESIGN	阿树	VIEW: 		MODEL TYPE: D-SUB		
CHECKED		UNIT: mm/in		PART NO.: X0215WT17B7		
APPROVED		SIZE: A4		DWG NO.: X-X0215WT17B7		
PRECISION CO., LIMITED				SCALE N/A	PAGE 1/1	REVISION A1

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED	TOLERAUCES

XK13 星城 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

www.helloxkb.com	www.helloxkb.cn	www.xk-dq.cn
------------------	-----------------	--------------

△