




Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:250V AC/minute

耐压电压: 250V AC/分钟

Temperature range:-25℃~+85℃

温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

Insulation resistance: $\geq 100\text{M}\Omega$



绝缘电阻: $\geq 100\text{M}\Omega$

Contact resistance: $\leq 10\text{m}\Omega$


接触电阻: $\leq 10\text{m}\Omega$

After environment testing: $\leq 20\text{m}\Omega$

环境试验后: $\leq 20\text{m}\Omega$



XKB: 0.7[0.028]



X1259 H V -06 -N0

① ②③ ④⑤ ⑥ ⑦

①Series No.

②Category: H-HSG

③Welding Board Angle: V-Straight 180°

④Row No.-Pin No.: XX-02P-15P

⑤ Plug the Pin & Special No.

⑥Material: N0-PA66 94V-0

⑦Color: Blank-Natural Color

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	1.25	3.05	9	10.00	11.80
3	2.50	4.30	10	11.50	13.00
4	3.75	5.55	11	12.50	14.30
5	5.00	6.80	12	13.75	15.50
6	6.25	8.05	13	15.00	16.80
7	7.50	9.30	14	16.25	18.00
8	8.75	10.55	15	17.50	19.30

X1259HV-06-N0	Nylon 66 UL 94V-0	1259BT
PART NO	Material	Suitable XKB Terminal

							DSND		DATE		SCALE: N/A	MODEL TYPE: 1.25mm Board In Connectors
ΔX					ANGULAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.: X1259HV-06-N0
ΔX					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X1259HV-06-N0
ΔX					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4	
ΔX					$16 < L \leq 63$	± 0.4						
MARK	DESCRIPTION				DATE	REVISED	APPROVED	$L > 63$	± 0.5			
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dn.cn www.helloxkb.com www.helloxkb.cn										WEIGHT 1.0g	SHEET 1/1	REVISION A0