




Specifications:

规格:

Voltage rating:400V AC/DC

额定电压: 400V AC/DC

Current rating:10A AC/DC

额定电流: 10A AC/DC

Withstanding voltage:1800V AC/minute

耐受电压: 1800V AC/分钟

Temperature range:-40°C-+105°C










温度范围: -40°C ~ $+105^{\circ}\text{C}$

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance:10mΩ Max

接觸電阻: 10mΩ Max



X2513 W R - 02 A S - LP SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2. Category: W-Wafer

3.Welding Board Angle:R-Stright 90°

4.Row No.Pin No:XX-02~08P

5.Special No:A-A Key(Black);B-B Key(Natural)

6.Special No:S-With Positioning Column

7. Material: LP-LCP 94V-0

8. Plating Category: SN-Bright Tin Plating

Poles	Dimensions(mm)	
	A	B
02	5.94	2.50
03	8.44	5.00
04	10.94	7.50
05	13.44	10.00
06	15.94	12.50
07	18.44	15.00
08	20.94	17.50

X2513WR-02AS-LPSN	LCP	Brass	X2513H
PART N0	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.50mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X2513WR-02AS-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X2513WR-02AS-LPSN
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5

www.helloxkb.com www.helloxkb.cn www.xk-dq.cn

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED