


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A2	N/A		焊脚电路图修正	2025.09.15	阿树
A3	N/A		焊脚电路图修正	2026.04.09	阿树



■ SPEAIFICATIONS

1.ELECTRICAL	
Con tact rating	0.1A,30VDC
Con tact resistance	50mΩ Max
Insulation resistance	100MΩ Min .at 250VDC
Dielectric strength	250VAC Min .for 60sec

2.MECHANICAL AND ENVIRONMENTAL

●Temperature ratong	Operating -15 to +55 storage.-25 to +65
● Operation	160±80gf
● Stroke	Lock Stroke 2.0±0.2mm Full stroke,2.5±0.2mm
● Operating life	Full load:1x10 ⁴ cycles N0 load:1x10 ⁵ cycles
● Con tact form	DPDT

PAPT NO	XKB8585-W-190
OPERATION	W:NO LOCK Z:LOCK

7	Contact	2	Phosphor Bronze	Plating silvering
6	Terminal	6	Brass	Plating silvering
5	Spring	1	Sus	Natural
4	Base	1	PBT	
3	Crochet Needle	1	Sus	Natural
2	Cover	1	POM	
1	Keystake	1	POM	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

FEATURES
Light operating force
Long term low con tact resistance
Momentary or lating operation
Compact spacing on PCB of 8.5mm
Short stroke 2.0mm to latch

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	KEY SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	XKB8585-W-190
APPROVED		SIZE:	A4	DWG NO.:	

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A3

