



Recommended PCB Layout
General Tolerance±0.05

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/ 分钟

Temperature range:-25 ℃-+85℃

温度范围: -25℃-+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X2026 W V -2x10-NOSN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:V-Straight 180°

4.Welding Way:Blank-DIP

5.Row No-Pin No:2xXX-2x02P~2x22P

6.Plug the Pin&Special N0:HF-Halogen Free

7.Material:N0-PA66 94V-0

8.Plating Category:SN-Bright Tin Plating

V01-All Gold Flash

9.Color:Blank-Natural Color ; BK-Black;WH-White

poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	6.00	4.80	2x09	16.00	20.00	18.80	2x16	30.00	34.00	32.80
2x03	4.00	8.00	6.80	2x10	18.00	22.00	20.80	2x17	32.00	36.00	34.80
2x04	6.00	10.00	8.80	2x11	20.00	24.00	22.80	2x18	34.00	38.00	36.80
2x05	8.00	12.00	10.80	2x12	22.00	26.00	24.80	2x19	36.00	40.00	38.80
2x06	10.00	14.00	12.80	2x13	24.00	28.00	26.80	2x20	38.00	42.00	40.80
2x07	12.00	16.00	14.80	2x14	26.00	30.00	28.80	2x21	40.00	44.00	42.80
2x08	14.00	18.00	16.80	2x15	28.00	32.00	30.80	2x22	42.00	46.00	44.80

X2026WV-2x10HF-NOSNBK	PA66 UL 94V-0 Black(Halogen Free)	Brass	Tin-Plated	X2026H
X2026WV-2x10-N0 SNWH	PA66 UL 94V-0 White		Tin-Plated	
X2026WV-2x10-N0 V01	PA66 UL 94V-0		Gold-Flash	
X2026WV-2x10-N0 SN			Tin-Plated	
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Housing

Wire to board connector

						DSND		DATE		SCALE: N/A	MODEL TYPE: 2.00mm Crimp Style Connectors
						DWN		DATE		VIEW:	PART NO.: X2026WV-2x10-N0SN
						CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2026WV-2x10-N0SN
						APPD		DATE		SIZE: A4	
						XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
											SHEET 1/1
											REVISION A0

units: mm

tolerance:

X.X ±0.2mm

X.XX ±0.1mm

X.XXX ±0.05mm

REVISIONS

UNSPECIFIED TOLERANCES

www.xk-dg.cn

www.helloxkb.com

www.helloxkb.cn